






HOT DAQ Solution

Data Acquisition | Data Integration

HPLC LFM



Database



Printer for Compliance

APIs to fetch records in JSON format for Data Integration with Enterprise Software

Apart from LFM & DFM, HOT DAQ Solution can acquire Data from any other Modbus Device connected on any type of bus or network like RS-485, RS-232, USB or Ethernet


The HOT DAQ Solution reads data from the attached Modbus device (Data Acquisition) and displays it on HMI Screen in real-time and populates DB. It allows to print last five readings and the corresponding Mean value for compliance. Data Integration is facilitated using APIs which can generate output in CSV, JSON or PDF format.


HOT DAQ Solution


Data Acquisition | Data Integration


Client Logo


HPLC Liquid Flow Meter - HOT DAQ



Run



Reset


System


Reports


Information





Hari Om Tatsat Technologies
HPLC Flowmeter

Mangal Prayogshala - Varanasi
M-6935
Date: 18-Apr-2026 Time: 12:36:46
Flow Rate in mL / minute

18-Apr-2026 12:37:55
Designed and Developed by
Hari Om Tatsat Technologies **HOT**

Hari Om Tatsat Technologies
 A-307/308, Shree Adinath Tower, Nancy Colony, Borivali (East), Mumbai – 400066.
 +91-9819336001 | info@hariomtatsat.co.in